

Flat magnetic grips, hard ferrite core, steel jacket

With bore hole and countersink

ORION[®]

Application:

Auxiliary materials with universal application during clamping, assembling, lifting and welding operations, and for installing in devices etc.

Version:

- With hard ferrite core
- Surface galvanised
- Magnetic shielding
- With bore hole and countersink
- Operating temperature up to 100°C

Advantage:

- Fastening option from inside with a screw



Art. no.	51146 760
Outer diameter	40 mm
Height	8 mm
Bore diameter	5.5 mm
Adherence strength	130 N

EAN-Code

4039247261949