

## PowerMaxx SB cordless hammer drill

Li-ion 10.8 V, 2 Ah

**metabo**<sup>®</sup>

### Version:

- Lightweight, compact cordless hammer drill with hammer function for drilling in masonry

### Delivery:

2x batteries, LC 40 charger, quick-action drill chuck, belt hook and bit depot, plastic case



<b>Art. no.</b>	<b>71037 401</b>
<b>Model</b>	PowerMaxx SB
<b>Battery included</b>	Yes
<b>Type of rechargeable battery/battery</b>	Li-Ion
<b>Rechargeable battery/battery capacity</b>	2 Ah
<b>Number of rechargeable batteries/batteries</b>	2 PCS
<b>Battery voltage</b>	12 V
<b>Max. drilling diameter in wood</b>	18 mm
<b>Max. drilling diameter in steel</b>	10 mm
<b>Max. drilling diameter in masonry</b>	10 mm
<b>Idle speed 1st gear min./max.</b>	0-360 rpm
<b>Idle speed 2nd gear min./max.</b>	0-1400 rpm
<b>Max. torque hard/soft</b>	34 / 17 Nm
<b>Min./max. drill chuck span width</b>	1.5-10 mm
<b>Max. impact rate</b>	2100 rpm
<b>Weight</b>	1.12 kg
<b>With working lights</b>	Yes
<b>With battery capacity display</b>	Yes
<b>With rubber-coated handle</b>	Yes
<b>With quick clamping system</b>	Yes
<b>With right/left-hand rotation</b>	Yes

### EAN-Code

4007430296856