

**PowerMaxx SB cordless hammer drill**  
Li-ion 10.8 V, 2 Ah



**Execution:**

- Lightweight, compact cordless hammer drill with hammer function for drilling in masonry

**Delivery:**

2x batteries, LC 40 charger, quick-action drill chuck, belt hook and bit depot, plastic case



Art. no.	71037 401
Brand	METABO
Manufacturer Part Number	600385500
Model	PowerMaxx SB
Battery included	Yes
Number of rechargeable batteries/batteries	2 PCS
Type of rechargeable battery/battery	Li-Ion
Rechargeable battery/battery capacity	2 Ah
Battery voltage	12 V
Max. drilling diameter in wood	18 mm
Max. drilling diameter in steel	10 mm
Max. drilling diameter in masonry	10 mm
Idle speed 1st gear min./max.	0-360 rpm
Idle speed 2nd gear min./max.	0-1400 rpm
Max. torque hard/soft	34 / 17 Nm
Min./max. drill chuck span width	1.5-10 mm
Max. impact rate	2100 rpm
Weight	1.12 kg
With working lights	Yes
With battery capacity display	Yes
With rubber-coated handle	Yes
With quick clamping system	Yes
With right/left-hand rotation	Yes
Gross Weight	2.995 kg
Product Group	745

**EAN**

4007430296856