

Female Headers

2.5mm pitch



SPECIFICATION:

Material

Shrapnel	Stainless Steel
Housing	PA66, UL94V-0
Clamp	Phosphor Bronze, Ni Plated

Electrical

Standard	IEC	
Rated Voltage	150V	250V
Rated Current	5A	6A
Wire Range	26-20AWG	0.14-0.5mm ²
Contact Resistance	20mΩ	
Insulation Resistance	500MΩ/DC500V	
Withstand Voltage	AC2000V/1Min	

Mechanical

Temperature Range	-40°C~+105°C
Strip Length	6-7mm

Size

Pitch	2.5mm(.098")
Poles	2P-12P

