



Hygro-Thermometer Clock

 **Triple display with Clock, Temperature and Humidity**
With user settable clock alarm

Features:

- Attractive design for desktop or wall mounting
- Three LCD displays of Time, Temperature and Humidity
- Max/Min memory with reset for Temperature and Humidity
- Switchable °C or °F temperature display
- 12/24 hour Clock with alarm function
- Complete with built-in tilt stand, wall mounting bracket and AAA battery



| Specifications: | 445702 |
|----------------------------|------------------------------------|
| Humidity range | 10 to 85% |
| Basic RH accuracy | ± 6% |
| Temperature range | 14 to 140°F (-10 to 60°C) |
| Basic Temperature Accuracy | 1.8°F/1°C |
| Dimensions | 4.3 x 2.8 x 0.8" (109 x 71 x 20mm) |
| Weight | 4oz (113g) |

Ordering Information:

445702Hygro-Thermometer Clock
409992Vinyl Pouch Carrying Case

