



Monocular brightfield microscope, 1000x, HC objectives

Observation Method -	Brightfield	Yes
Transmitted Light	Simple polarized light	As optional
Main Body	Туре	Upright
	Construction material	Aluminum die-cast
	Trasportation handle	Yes
Head	Туре	Monocular
	Inclination	30°
	360° rotating	Yes
	Fixing screw for eyepieces	Yes
	Tube inner diameter (mm)	23
Eyepieces	Field number (mm)	18
	Magnification	10x
	High eyepoint (for glass wearers)	Yes
	Pointer	As optional
	Micrometric scale	As optional
	Diameter of micrometer glass (mm)	20
Nosepiece	Positions	Quadruple
	Reversed	Yes
	Bi-directional	Yes
	Rotation on ball bearings	Yes
	Objective thread	RMS
Objectives	Optical system	160
	Anti-fungus treatment	Yes
	Parfocal distance (mm)	45
	Standard magnifications	40x-1000x
	Туре	HC
	Objectives included	4x/0.10, W.D. 18 mm
		10x/0.25, W.D. 7 mm
		40x/0.65, W.D. 0.53 mm
		100x/1.25 (Oil/Water),
		W.D. 0.13 mm
Ctown	T	Davida lavas
Stage	Type	Double layer
	Dimensions (mm)	125x115
	Moving mechanism	Rack and pinion
	Moving range (mm)	70x30
	Material	Anti-scratch painting
	Specimen holder	Yes
	Slide number	1
	X-Y movement	Yes
	X-Y Vernier scale	Yes
	Vernier scale accuracy (mm)	0.1

Condenser - Single Position	Туре	Abbe
	Numerical aperture (N.A.)	1.25
	Centrable	Pre-centered
	Focusable	By rotation
Focusing System	Туре	Coaxial coarse & fine
	Coarse total travel (mm)	18
	Fine total travel (per single rotation) (mm)	0.4
	Fine graduations	100
	Fine resolution (µm)	4
	Upper stop to prevent contact	Yes
	Adjustable tension	Yes
Transmitted Illumination	Туре	X-LED
	X-LED type	X-LED2
	Light source power (W)	3
	Brightness control	Manual
	Lifetime (hours)	> 65,000
	Temperature (K)	6,300
	Max. required power (W)	6
Power Supply for	Туре	External
Transmitted	Microscope connector	Jack, 2.1 mm
Illumination	Power plug type	Multi-plug (EU, UK, US)
	Input voltage	100/240 Vac, 50/60 Hz
	Output voltage	6 Vdc 2.5 A
Accessories Included	Dust cover	Yes
	Immersion oil (10ml)	Yes
	Tension adjustment tool	Yes
	User Manual	Digital version (downloadable)
		_ ig.iai i croisii (aciiiiicaaaici)
Additional Information		
		External rechargeable battery pack (as optional).
Product Dimensions	Height (mm)	370
	Width (mm)	235
	Depth (mm)	290
Product Weight	(kg)	6.5
	,	