

Item no.: 1567899 – Black	1565384 – Red	1567902 – White
1564676 – Blue	1567904 – Yellow	1567900 – Green
1567901 – Brown	1567903 – Grey	1570377 – Orange
1570378 – Violet	1567905 – Green/Yellow	



Data Sheet

YV Jumper Wire 0.2 mm²

Version 11/13

Jacket, outer dimension.....	PVC 1.1mm
No. of conductors.....	1 x 0.5mm
Strand per conductor.....	0.2 sqmm
Length.....	100 meter
Conductor material	Tinned - copper
Insulation material (with thickness).....	PVC 0.3mm
Core diameter.....	0.5mm
Insulation resistance.....	Min 200M ohm x km
Conductor resistance.....	Max 110 Ω /KM
Maximum dielectric strength.....	800V / AC
Temperature range.....	-20 to +70° C
Rated voltage.....	AC 50V / DC 75V
Rated current.....	1.6A
Conductor structure.....	One core