



RegLED CCT

REGLED CCT 4W 313MM I

Reglette LED downlight with variable light colour warm, white, cold

Order code 74075

EAN 8002219743855

Technical specifications

Absorbed Power	4 W
Supply voltage type	AC
Nominal voltage (AC)	230 Vac
Ambient temperature (min)	-20 °C
Ambient temperature (max)	40 °C
Insulation class	II
CCT light tone	3000 K, 4000 K, 5000 K
Colour consistency	SDCM3
CRI color rendering	>80
Ballast	For constant current LED
Efficiency	85 lm/W
Frequency (max)	60 Hz
Frequency (min)	50 Hz
Glow wire strength	850 °C - 30s.
MTBF driver	30000 h
Luminaire flux	340 lm
Voltage supply range (max)	265 V
Voltage supply range (min)	180 V

Installation and applications


Environment	Offices
Application	Shelves, Shops

Mechanical specifications


Height	30 mm
Length	313 mm
Width	22 mm
Weight	0.1 Kg
Colour housing	White
Protection grade IP	IP20
Protection grade IK	IK05

Certifications and norms

UK SI 2021 No. 1095, EN IEC 55015:2019 + A11:2020, EN IEC 61000-3-2 :2019, EN 61547:2009, EN 62471:2008, EN IEC 60598-1:2021, EN 60598-2-1:1989, EN IEC 63000:2018, EN 62493:2010, EN 61000-3-3:2013



N° max moduli in serie 10



Supplied accessories



424020004
GR ACCESSORY RGL LEDECO



424020003
CONNECTION PLUG 150 RGL
LEDECO



424020006
MAIN POWER L1500 REGLED
ECO

Accessories



424020009
CONNECTION PLUG 2MT RGL
LEDECO



424020005
CONN PLUG 1.5MT RGL
LEDECO