


CUBE20S DIGITAL INPUT MODULE DI4

4x24VDC Time Stamp ETS

Expansion module
DI4 - (E) ETS

[Link to Product](#)

Illustration



Product may differ from Image

Approvals



Input	
Sensor supply US	24 V DC (EN 61131-2), max. 500 mA per module
Type	NPN (EN 61131-2)
Input filter	max. 100 ns
Galvanic isolation	500 V DC between inputs and internal communication
Internal communication	
Module Supply	via system connection
Current consumption	max. 85 mA
General data	
Protection	IP20
Connection	Spring clamp plug-in terminals: max. 1.5 mm ² (AWG 16)
Mounting method	DIN-rail mountable (EN 60715)
Temperature range	0...+60 °C (storage temperature -20...+70 °C)
Dimensions H × W × D	109×12.9×76.5 mm
Diagnostic	
Communication status	via LED
Diagnostic via LED	per module and channel
Diagnostic via BUS	per module
Monitoring - under voltage	no
Monitoring - no voltage	yes
Short circuit and overload	yes
Commercial data	
country of origin	TH
customs tariff number	85389099
minimum order quantity	1