



EPPi® Rastereinsätze

K = Polypropylen (PP)
N = Karton

| Fächer für Röhrchen | Höhen | | | | | |
|-------------------------|-------------|-------------|-------------|-------------|-------------|-------------|
| | 15 mm | 25 mm | 30 mm | 40 mm | 65 mm | 80 mm |
| | Artikel-Nr. | Artikel-Nr. | Artikel-Nr. | Artikel-Nr. | Artikel-Nr. | Artikel-Nr. |
| 16x16 bis ca. 7,2 mm Ø | RB10151616N | RB10251616N | RB10301616N | RB10401616N | RB10651616N | RB10801616N |
| 15x15 bis ca. 7,7 mm Ø | RB10151515N | RB10251515N | RB10301515N | RB10401515N | RB10651515N | RB10801515N |
| 14x14 bis ca. 8,3 mm Ø | RB10151414N | RB10251414N | RB10301414N | RB10401414N | RB10651414N | RB10801414N |
| 13x13 bis ca. 9,0 mm Ø | RB10151313N | RB10251313N | RB10301313N | RB10401313N | RB10651313N | RB10801313N |
| 12x12 bis ca. 9,8 mm Ø | RB10151212N | RB10251212N | RB10301212N | RB10401212N | RB10651212N | RB10801212N |
| 11x11 bis ca. 10,8 mm Ø | RB10151111N | RB10251111N | RB10301111N | RB10401111N | RB10651111N | RB10801111N |
| 10x10 bis ca. 12,0 mm Ø | RB10151010N | RB10251010N | RE10301010K | RB10401010N | RB10651010N | RB10801010N |
| 9x9 bis ca. 13,6 mm Ø | RB10150909N | RB10250909N | RE10300909K | RB10400909N | RB10650909N | RB10800909N |
| 8x8 bis ca. 15,0 mm Ø | RB10150808N | RB10250808N | RE10300808K | RB10400808N | RB10650808N | RB10800808N |
| 7x7 bis ca. 17,3 mm Ø | RB10150707N | RB10250707N | RE10300707K | RB10400707N | RB10650707N | RB10800707N |
| 6x6 bis ca. 20,3 mm Ø | RB10150606N | RB10250606N | RB10300606N | RB10400606N | RB10650606N | RB10800606N |
| 5x5 bis ca. 24,5 mm Ø | RB10150505N | RB10250505N | RE10300505K | RB10400505N | RB10650505N | RB10800505N |
| 4x4 bis ca. 30,8 mm Ø | RB10150404N | RB10250404N | RE10300404K | RB10400404N | RB10650404N | RB10800404N |
| 3x3 bis ca. 41,2 mm Ø | RB10150303N | RB10250303N | RE10300303K | RB10400303N | RB10650303N | RB10800303N |

