

## VB RJ45 LaR -VB RJ45 LaR Cat.6A PUR 5.0m



Part number	09 48 858 5745 050
Specification	VB RJ45 LaR -VB RJ45 LaR Cat.6A PUR 5.0m
HARTING eCatalogue	<a href="https://b2b.harting.com/09488585745050">https://b2b.harting.com/09488585745050</a>

### Identification

Category	Cable
Series	RJ45
Specification	Pre-assembled on both sides
Connector 1	HARTING VarioBoot RJ45 Preferred directions left/right
Connector 2	HARTING VarioBoot RJ45 Preferred directions left/right
Type of cable	Copper cable (round)
Description of the cable	Wiring 1:1 Halogen-free oil resistant

### Version

Number of cores	8
Core structure	4x 2 Twisted Pair

### Technical characteristics

Limiting temperature	-30 ... +75 °C unmoved -5 ... +50 °C moved
Degree of protection acc. to IEC 60529	IP20
Cable length	5 m
Transmission characteristics	Cat. 6 <sub>A</sub> Class E <sub>A</sub> up to 500 MHz
Data rate	10 Mbit/s 100 Mbit/s 1 Gbit/s 10 Gbit/s



Pushing Performance

## Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Yellow

## Specifications and approvals

Specifications	IEC 11801
	IEC 61156-6

## Commercial data

Packaging size	1
Country of origin	Czechia
European customs tariff number	85444290
eCl@ss	27060390 Ready-made data cable (unspecified)