

NYS236

mono 2 pole 1/4" jack to jack adapter



Article Variations

Article Name	Details	Packaging
NYS236	mono 2 pole 1/4" jack to jack adapter	Single Packaging
NYS237	mono 2 pole 1/4" plug to plug adapter , full metal	Single Packaging
NYS238	mono 3 pole 1/4" jack to jack adapter	Single Packaging
NYS239	mono 3 pole 1/4" plug to plug adapter , full metal	Single Packaging

Technical Information

Product

Title	NYS236
Connection Type	

Electrical

Contact resistance	$\leq 10\text{m}\Omega$
Insulation resistance	$\geq 2000\text{M}\Omega$
Dielectric strength	50Hz 500VAC

Mechanical

Insertion and Withdrawal force	2-35N
Lifetime	>1000mating cycles

Material

Fixed Sleeve	ABS
Housing	Brass
Sleeve Nose	Brass
Contact	Bronze
Contact/Soldering Contact	Tinned and Cerium