



RCG inkorthaak (Grade 10)




Type	Veilige werklast (kg)	P (mm)	L (mm)	O (mm)	W (mm)	Gewicht (kg/st/m)	Artikelnummer
RCG-6	1.400	43.9	77.3	7.5	41.6	0.2	2642006
RCG-8	2.500	52.2	92.6	10.3	53.3	0.4	2642008
RCG-10	4.000	72.3	126.5	13.3	72.2	0.9	2642010
RCG-13	6.700	90.0	163	16.7	96.2	1.9	2642013
RCG-16	10.000	101	185	19.3	112.3	3.3	2642016

REGS inkortooghaak met veiligheids pin (Grade 10)



Type	Veilige werklast (kg)	P (mm)	D (mm)	E (mm)	L (mm)	O (mm)	W (mm)	Gewicht (kg/st/m)	Artikelnummer
REGS-8	2.500	74.3	12.0	15.9	110.6	10.5	55.6	0.5	2648108
REGS-10	4.000	91.5	14.5	20.6	134.5	13.3	69.8	1.0	2648110
REGS-13	6.700	120	20.4	26.9	175	15.9	91.6	2.2	2648113

RCCS inkortklauw met veiligheids pin (Grade 10)



Type	Veilige werklast (kg)	P (mm)	W (mm)	L (mm)	Gewicht (kg/st/m)	Artikelnummer
RCCS-8	2.500	63.3	91.5	50	0.4	2651008
RCCS-10	4.000	81.0	113	59	0.8	2651010
RCCS-13	6.700	105.0	149	79	1.7	2651013