
PRODUCT-DETAILS

232EC6W

Industrial Connectors, 2P+E, 32A, 200 ... 250 V



General Information

Extended Product Type	232EC6W
Product ID	2CMA101142R1000
EAN	7392696011426
Catalog Description	Industrial Connectors, 2P+E, 32A, 200 ... 250 V
Long Description	Industrial Connectors, 2P+E, 32A, 200 ... 250 V Clock Position Of Grounding Contact 6 hour Color code Blue

Ordering

E-Number (Sweden)	E2416797
E-Number (Finland)	2420119
E-Number (Norway)	1540728
EAN	7392696011426
Country of Origin	Czech Republic (CZ)
Minimum Order Quantity	10 piece

Dimensions

Product Net Width	98 mm
Product Net Height	98 mm

Product Net Length	195 mm
Product Net Depth / Length	195 mm
Product Net Weight	0.28 kg

Container Information

Package Level 1 Width	390 mm
Package Level 1 Depth / Length	175 mm
Package Level 1 Height	195 mm
Package Level 1 Gross Weight	2.8 kg
Package Level 1 EAN	7392696016766
Package Level 1 Units	box 10 piece

Technical UL/CSA

Tightening Torque UL/CSA	10.6 in-lb
-----------------------------	------------

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CMC700005D0001
Declaration	2CMC700005D0001
Environmental Information	2CMC000056M0000
RoHS Information	2CMC700005D0001
SEMKO Certificate	1620515
REACH Declaration	2CMC700005D0001

Additional Information

Additional Information	2P+E
Ambient Temperature	-25 ... 40 °C
Cable Cross-Section	2.5 ... 6 mm ²
Cable Diameter	22 mm
Cable Entry Position	Swivel
Color	Blue
Connection Type	Screw Clamp
Degree of Protection	IP67
Enclosure Material	Plastic (PA)
Frequency (f)	50 Hz 60 Hz
Function	Connector
Housing Material	Plastic (PA)
Invoice Description	Ind. P&S#232EC6W
Material	Plastic
Number of Poles	3

Order Multiple	10 piece
Product Main Type	EC
Product Name	Industrial Connector
Protection Type	Watertight
Rated Current (I_n)	32 A
Rated Voltage (U_r)	200 ... 250 V
Recommended Screw Driver	PH2
Standards	IEC 60309-1, -2
Suitable for Product Class	IEC Industrial Plugs and Sockets
Instructions and Manuals	2CMC700014C0016
RAL Number	RAL 7012 - Basalt Grey

Classifications

eClass	27440509
UNSPSC	39120000

Technical

Wire Size	12 ... 10 AWG
Tightening Torque	1.2 N·m

Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Easy & Safe → Connectors

