

Micrometer

Narrow measuring surfaces

Mitutoyo

Application:

For measuring narrow external recesses.

Version:

- Semi-gloss chrome-plated scale drum and sleeve
- Carbide-tipped measuring faces or hardened blades
- Friction coupling for consistent, repeatable measuring force
- Non-rotating measuring spindle

Advantage:

- Accesses hard-to-reach measuring points

Delivery:

Includes box, adjustment wrench



Art. no.	32116 546
Min./max. length measuring range	175-200 mm
Vernier scale	0.01 mm
Measuring surface depth	6.5 mm
Measuring spindle increments	0.5 mm
Bracket depth	118 mm
Measuring surface width x Measuring surface depth	0.75 x 6.5 mm
Spindle clamping	No
Error limit	5 µm
Display	Nonius
Calibration Group	D
Min./max. measurement force	3-8 N

EAN-Code

4946368847382