

Precision indicator

MAHR 1003 precision pointer Millimess



Application:

For measuring lengths. Ideal for measuring instruments and flatness and straightness measurements

Version:

- Shock resistant
- Ball-guided measuring pin
- Connection for wire lifter
- Pointer fine adjustment
- Adjustable tolerance marks
- Measuring mechanism on ruby bearings

Delivery:

In case



Art. no.	33163 130
Scale value	0.001 mm
Length measuring range	0.1 mm
Shaft diameter	8 mm
Shaft length	20 mm
Error limit	1.2 μm
With free stroke	Yes
Measurement force	1 N
Reversal error	0.5 μm
Repeat accuracy	0.5 μm
Calibration Group	K
DIN	879

EAN-Code

4059192014100