

## Drawer with full extension for drawer cabinet, system 700


Depth 600 mm

### Application:

For individual fitting of the HK cabinet housing 700 B. The drawers can be installed in the housing in arbitrary sequence. The sum of the front heights must be the effective height of the housing.

### Execution:

- Made of sheet steel metal with a reinforced, perforated bottom (25 mm hole grid)
- Run on Delrin rollers in rails which are suspended in the housing with plug caps
- Inner sides slotted all around, for attaching and fixing insert material such as compartment rails and dividers
- Equipped with aluminium handle strip, paper and cellon strips and lateral cover caps
- SOFT-CLOSE-AUTOMATIC for smooth and silent drawer closing, see no. 50392 005



<b>Art. no.</b>	<b>50300 420</b>
<b>Brand</b>	HK
<b>Manufacturer Part Number</b>	50300420
<b>Drawer front height</b>	180 mm
<b>Drawer cabinet height</b>	100 mm
<b>Mount height</b>	160 mm
<b>Drawer width (inner dimension)</b>	600 mm
<b>Drawer depth (inner dimension)</b>	600 mm
<b>Drawer surface</b>	0.36 m <sup>2</sup>
<b>Pullout type</b>	Full extension
<b>Load-carrying capacity</b>	100 kg
<b>Drawer with slots</b>	Yes
<b>Perforated drawer base</b>	Yes
<b>Material</b>	Sheet steel
<b>Colour of front</b>	Optional
<b>Box colour</b>	Light grey RAL 7035
<b>Surface</b>	Powder-coated
<b>Gross Weight</b>	16.100 kg
<b>Product Group</b>	5BB

### EAN

4039247693474