

SOLID PC 3828 13 G



Sample photo

Order symbol: PC 3828 13 G
Product nbr: 5330363
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074005564
EI. number:
 Finland: 3423717
 Electric No. Italy: 7401050
 Electric No. Sweden: 2539422

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions: Length Width Height Accessories:

Dimensions:	Length	Width	Height	Accessories:
mm:	378	278	130	EKPXT Mounting plate isolated
inch:	14.9	10.9	5.1	EKV 22 DIN-35 Mounting rail
				EKV 32 DIN-35 Mounting rail
				EKPZR Extension frame

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover screws material:	Polyamide
Cover colour:	RAL 7035 -light grey
Cover screws colour:	Grey
Gasket material:	Polyurethane

Rating:

Ingress Protection (EN 60529):	IP66/IP67
Impact Resistance (EN 62262):	IK08/IK09
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance:	UL 508
Flammability Rating:	UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C:	960
NEMA Class:	NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12

Temperatures:

Temperature °C (short term):	-40 ... 120 °C
Temperature °C (continuous):	-40 ... 80 °C
Temperature °F (short term):	-40 ... 250 °F
Temperature °F (continuous):	-40 ... 175 °F

Certificates:

SGS Fimko

Accessories:

EKPVT	Mounting plate
-------	----------------

