


## LEDs DECO FLEX

---





---

*Product line drawing with numbers*  
*RGB Add-on | BASE*

## Technical data

| Product description | Type of installation | Number of lighting outlets | Nominal wattage | Beam angle | Operating mode                | Luminous flux |
|---------------------|----------------------|----------------------------|-----------------|------------|-------------------------------|---------------|
| RGB Add-on          | Adhesive             | 24                         | 3.60 W          | 113 °      | Electronic control gear (ECG) | 65.6 lm       |
| BASE                | Adhesive             | 36                         | 18.00 W         | 113 °      | Electronic control gear (ECG) | 98.4 lm       |
| EXTENSION KIT       |                      |                            |                 |            |                               |               |

| Product description | Luminous flux | Luminous intensity | Color rendering index Ra | Length   | Width   | Height |
|---------------------|---------------|--------------------|--------------------------|----------|---------|--------|
| RGB Add-on          | 65.6 lm       | 0.580 cd           | 22.3                     | 640.0 mm | 10.0 mm | 2.0 mm |
| BASE                | 98.4 lm       | 0.866 cd           | 22.3                     | 960.0 mm | 10.0 mm | 2.0 mm |
| EXTENSION KIT       |               |                    |                          |          |         |        |

| Product description | Height | Body material | Product color     | Cover material | Ambient temperature range | Equipment |
|---------------------|--------|---------------|-------------------|----------------|---------------------------|-----------|
| RGB Add-on          | 2.0 mm | Epoxy resin   | Transparent/White | Epoxy resin    | ...+25 °C                 | LED       |
| BASE                | 2.0 mm | Epoxy resin   | Transparent/White | Epoxy resin    | ...+25 °C                 | LED       |
| EXTENSION KIT       |        |               |                   |                |                           | ...+25 °C |

| Product description | Equipment | Equipped with lamp | Adjustable | Dimmable | Color management (RGB) | With on/off switch |
|---------------------|-----------|--------------------|------------|----------|------------------------|--------------------|
| RGB Add-on          | LED       | Yes                | Yes        | Yes      | Yes                    | No                 |

|               |     |     |     |     |     |    |
|---------------|-----|-----|-----|-----|-----|----|
| BASE          | LED | Yes | Yes | Yes | Yes | No |
| EXTENSION KIT |     | No  |     |     | No  | No |

| Product description | With on/off switch | Accessories    | Standards | Protection class | Type of protection | Protection against ignition and fire |
|---------------------|--------------------|----------------|-----------|------------------|--------------------|--------------------------------------|
| RGB Add-on          | No                 | Connection     | CE        | II               | IP20               | F, MM                                |
| BASE                | No                 | Remote control | CE        | II               | IP20               | F, MM                                |
| EXTENSION KIT       | No                 |                | CE        |                  |                    | F, MM                                |

## **Application advice**

---

For more detailed application information and graphics please see product datasheet.

## **Disclaimer**

---

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.