



## Terminal block250A/63A



Powering Business Worldwide™

Part no. **BPZ-KB-24/250**

Article no. **289971**

### Delivery programme

Mounting type			Floor standing distribution board Surface mounted Flush mounted
Degree of Protection			IP20
Mounting position			universal
Number of poles			4 pole
Width		mm	422
Depth		mm	50
Height		mm	40
Number of clamping units per pole			12
Rated device current		A	250

### Technical data ETIM 6.0

Energy distribution systems (EG000015) / Distributor assembly terminal blocks (EC001894)			
Electric engineering, automation, process control engineering / Electrical insulation and connecting material / Energy distribution system / Distributor assembly terminal blocks (ecI@ss8.1-27-40-06-09 [ACO381008])			
Height		mm	84
Width		mm	427
Depth		mm	51
Max. rated current		A	250
Number of poles			4
Conductor cross section flexible (fine-strand) with cable end sleeve		mm <sup>2</sup>	1.5 - 10
Conductor cross section solid (solid, stranded)		mm <sup>2</sup>	0 - 0
Number of clamp positions per pole			12
With PE-rail			No
With N-rail			Yes