



**Part no.: 529604**  
**UM60-450**  
**Deflecting mirror**

Figure can vary

## Contents

- Technical data
- Dimensioned drawings

Part no.: 529604 – UM60-450 – Deflecting mirror

## Technical data

### Basic data

|                           |                   |
|---------------------------|-------------------|
| Series                    | UM                |
| Type, columns and mirrors | Deflecting mirror |

### Mechanical data

|                              |  |
|------------------------------|--|
| Dimension (W x H x L)        | 25 mm x 68 mm x 520 mm                 |
| Net weight                   | 1,000 g                                |
| Housing color                | Yellow, RAL 1021                       |
| Type of fastening            | Groove mounting<br>Swivel mount        |
| Suitable for sensor          | MLC 500, MLC 300 safety light curtains |
| Protected field height up to | 450 mm                                 |
| Mirror length                | 510 mm                                 |


### Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 70099200 |
| eCl@ss 8.0            | 27279207 |
| eCl@ss 9.0            | 27273605 |
| ETIM 5.0              | EC002467 |
| ETIM 6.0              | EC002467 |

## Dimensioned drawings

All dimensions in millimeters

Mirror




L Length = 520 mm  
 SL Mirror length = 510 mm

Mounting distances




A Max. 500 mm

Mounting with BT-UM60 standard bracket



- A Lateral
- B Rear side
- C Adjustable at an angle (0 - 90°)

Mounting with BT-SSD swiveling mounting bracket



- A Rear side
- B Lateral 45°