


## RMIE 11/24 INPUT RELAY

IN: 24 VDC - OUT: 125 VAC/DC / 1 A

1 relay; 1 NO/NC contact  
24 V DC  
Screw terminals

### [Link to Product](#)

#### Illustration



Product may differ from Image

#### Utilization category

AC-1	1 A (50 V AC)
AC-15	0.5 A (50 V AC)
DC-13	0.25 A (50 V AC)

#### Input

Connection voltage - current	24 V DC (19.2...30 V DC) - 12 mA
LED display	LED (yellow)

#### General data

Mech./ elect. life	200.000.000 switching cycles/load dependent
Test isolation voltage	1.5 kV
Mounting method	DIN-rail mountable TH35 (EN 60715)
Temperature range	-20...+60 °C (storage temperature -40...+80 °C)

**Output**

Switching voltage	max. 125 V AC/DC
Switching current per output	max. 1 A
Min. load current	1 mA
Power rating (voltage dependent)	max. 60 VA/30 W
Switching frequency	max. 0.1 Hz (with load)
Contact material	Pd Ni-Au Rh
Energize/release/contact bounce time	10/15/2 ms

**Commercial data**

country of origin	CZ
customs tariff number	85364900
minimum order quantity	1