



SIMATIC ET 200SP, BASEUNIT BU15-P16+A0+2D/T, BU-TYPE A1, PUSH-IN TERMINALS, W/O AUX-TERMINALS, NEW LOAD GROUP, WXH: 15MMX117MM, WITH TEMPERATURE MEASURING

<b>Product type designation</b>	
<b>Supply voltage</b>	
Rated value (DC)	24 V
External protection of power supply lines	Yes; 24 V DC/10 A miniature circuit breaker with type B or C tripping characteristic
<b>Current carrying capacity</b>	
up to 60 °C, max.	10 A
<b>Analog inputs</b>	
Thermocouple (TC)	
Temperature compensation	
— internal temperature compensation	Yes
<b>Galvanic isolation</b>	
between backplane bus and supply voltage	Yes
between the potential groups	Yes
<b>Isolation</b>	
Isolation checked with	707 V DC (type test)
<b>Dimensions</b>	
Width	15 mm
Height	117 mm
<b>Weights</b>	
Weight, approx.	40 g

last modified:

12.03.2015