

Product information

87 00 100

KNIPEX Cobra® XS

Water Pump Pliers

DIN ISO 8976





- Optimum accessibility, even in confined spaces: particularly compact design, very slim head
- One-handed fine adjustment by pushing for the simplest adjustment to different workpiece sizes
- Long-lasting secure grip ensured by high wear resistance
- Gripping capacity Ø 28 mm, width across flats up to 24 mm at only 100 mm length
- Box joint: high quality and durability provided by dual guide
- Gripping surfaces with specially hardened teeth, hardness approx. 60 HRC
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Pinch guard prevents operators' fingers being pinched
- Fine adjustment with 11 adjustment positions



General	
Article No.	87 00 100
EAN	4003773085836
Pliers	grey atramentized
Head	polished
Handles	embossed, rough surface
Weight	62 g
Dimensions	100 x 30 x 10 mm
Standard	DIN ISO 8976
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Adjustment positions	11
Kapazität für Rohre (Zoll)	Ø 1 Inch
Capacities for nuts	24 mm
Capacities for pipes (diameter)	Ø 28 mm


technical change and errors excepted

KNIPEX Quality – Made in Germany





Self-locking and durable – all part of genuine KNIPEX water pump pliers











KNIPEX Quality – Made in Germany





