

---

Item no.: 243-144  
Product description: MICRO PUSH-WIRE CONNECTOR FOR JUNCTION BOXES;  
4-CONDUCTOR TERMINAL BLOCK; PUSH-WIRE  
CONNECTION

---



Packing unit 1000 10\*100 pieces

pole count	4
Cross section from [AWG]	20 AWG
Cross section to [AWG]	24 AWG
Diameter from	0,4 mm
Diameter to	0,5 mm
Measured voltage EN	100 V
Measured shock voltage	1,5 kV
Pollution degree	2
Current intensity EN	6 A
Weight	0,81 g
Color	transparent
Wiring type	Side-entry
No. of connection Points	4
No. of potentials	1
Height	6,8 mm
Height	0,268 in
Width	10 mm
Width	0,394 in
Depth	10 mm
Depth	0,394 in
Strip length from	5 mm
Strip length to	6 mm
Strip length	0,22 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
243-144	ABS	04-HG476172-PDA	100	6	0,5-0,75
243-144	CSM	017956	100	6	0,5-0,75
243-144	LR	04/20013(E1)	100	6	0,5-0,75
243-144	RMR	11130002	100	6	0,5-0,75
243-144	RosTesT	B09523	100	6	0,5-0,75

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected