ZCKD01

limit switch head ZCKD - metal end plunger





Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKD
Head type	Plunger head
Product compatibility	XCKS
Associated body	ZCKS2H29 ZCKS8H29 ZCKS8 ZCKS5H29 ZCKS2 ZCKSD39 ZCKS5 ZCKSD31 ZCKSD35H29 ZCKS6 ZCKS9 ZCKS9H29 ZCKS9H29 ZCKS6H29 ZCKS031H29 ZCKSB31H29 ZCKSCH29 ZCKSD31H29 ZCKSD31H29 ZCKSD37 ZCKSD35 ZCKS1 ZCKSD37 ZCKSD37
Movement of operating head	Linear
Type of operator	End plunger spring return metal
Type of approach	Vertical approach, 1 direction

Complementary

Switch actuation	On end
Positive opening	With
Head material	Plastic

Environment

Ambient air temperature for operation	-13158 °F (-2570 °C)
Ambient air temperature for storage	-40158 °F (-4070 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22416-LIMIT SWITCHES,IEC,XCKL	
Discount Schedule	Т	
GTIN	00785901780816	
Package weight(Lbs)	0.09 lb(US) (0.039 kg)	
Returnability	No	
Country of origin	FR	

Packing Units

Package 1 Height	0.330 dm
Package 1 width	0.630 dm
Package 1 Length	0.780 dm

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	☑ REACh Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EPEU RoHS Declaration
Mercury free	Yes
RoHS exemption information	€Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

	•	
Warranty	18 months	