

Clamps



Version:

- Heat-treated steel
- Painted
- With self-locking trapezoidal thread spindle and end safety device.
- With flat support

Art. no.	26157 010
Min./max. support plate height	38-50 mm
Diameter	31 mm
Head diameter	31 mm
Max. force range	25 kN
Centring diameter	12 mm

EAN-Code

402077207239 1

