

Electronic workshop vernier callipers

TWIN-CAL IP67 without blade tips

 **TESA**

Application:

For measuring external and internal dimensions.

Execution:

- ON
- Zero setting at any position
- mm/inch switch-over
- Auto off
- ABS function
- Without blade tips

Advantage:

- IP protection guaranteed even with data transfer connection
- Soft Touch for comfortable handling

Delivery:

In a case, with battery (1 x 3 V lithium type CR 2032)



| | |
|---|--------------------|
| Art. no. | 31154 181 |
| Brand | TESA |
| Manufacturer Part Number | 00530426 |
| Min./max. length measuring range | 0-800 mm |
| Data transmission type | TLC |
| IP protection class | IP 67 |
| Length of jaw | 150 mm |
| Measuring tips | No |
| Fine adjustment | No |
| Digit increment | 0.01 mm |
| Inner measurement scales | 20 mm |
| Type of locating | With locking screw |
| Display | Digital |
| Calibration Group | A |
| Number of rechargeable batteries/batteries | 1 PCS |
| Battery designation | 3V CR2032 Lithium |
| ISO | 13385-1 |
| Gross Weight | 5.381 kg |
| Product Group | 362 |

EAN

763004110638 1