

End-cutting nippers for electronics

End-cutting nippers, short head, with small chamfer



Application:


For precision cutting tasks in electronics and precision mechanics fields.

Execution:

- Ball bearing chrome steel
- Blades also inductively hardened
- Pushed-through precision joint
- Low-friction double spring for smooth, even opening action

Advantage:

- Mirror-finished surface with fine oil film to protect against rust, no interference in the circuit by flaking chrome parts
- Safe, ergonomic and fatigue-free working thanks to two-component handles



Art. no.	53105 030
Brand	KNIPEX
Manufacturer Part Number	64 32 120
Length	120 mm
Max. soft wire diameter cutting capacity	1.5 mm
Head design	With small bevel
Surface	Plain
Material of handle	2-component plastic
Gross Weight	0.097 kg
Product Group	535

EAN

4003773017820