



- Protection level: IP67  
 - Temperature range: -25°C ... +85°C

Electrical data:  
 -Rated voltage: 15-30V DC  
 -Nominal: 2 A per Contact  
 -Current: 6 A max total

7	09070010015000	PVC, 2x AWG 20 + 8x AWG 24, black	10
6	09070010015100		5
5	09070010015300		2
4	09070010010000	PUR, 2x AWG 20 + 8x AWG 24, black	10
3	09070010010100		5
2	09070010010400		3
1	09070010010300		2
Cont. no	HARTING part no.	Type of cable	Dim. a[m]

	All rights reserved Department HCS - RO	Tech. Character.		Free size tol.		According to production drawing	
		Created by COSTEA Costea	Inspected by 402676 Gross	Standardisation MUNTEANV Muntean	Date 2020-08-25	State Final Release	
HARTING Customised Solutions D-32339 Espelkamp		Title har-SAB M8/4/3p PAC w/o LED			Doc-Key / ECM-Nr. 100905089/UGD/000/B 500000178719		
		Type TB	Number 0907001001XX00		Rev. B	Page 1/1	