

## ELMCL21L

European Region

### HIGH-TECH

- Advanced Azoteq IQ Switch® circuitry
- Pulse width modulation
- Adjustable brightness
- Up to 24-hour run time



### BRIGHT

- Cree® XRE lifetime LED provides a maximum of 110 lumens



### WATERPROOF

- Meets IEC 60529 IPX7 standards – 1 m for 30 minutes



### DURABLE

- Machined aircraft aluminum casing
- S500 Poly (organo) siloxane coated shatterproof lens



The ELMCL21L has a wealth of high-tech features. An advanced Azoteq IQ Switch® adjusts brightness to your desired level. Pulse width modulation maximizes battery life, allowing 24 hours of runtime on a low light setting. The shatterproof lens is coated with S500 Poly(organo) siloxane for superior hardness and weathering resistance.

In addition the light boasts convenience features like a sturdy belt clip, a comfortable hand grip and an automatic 30-minute shutoff. The pushbutton tail-switch regulates brightness with the touch of a finger. Powered by light weight, long-lasting lithium batteries, the ELMCL21L is your lighting choice when only the best will do.




**Before Using Your Flashlight:**  
Please read all instructions and cautionary markings on the package and light

European Region

### Product Detail:

<b>Designation:</b>	Energizer Lithium LED Light 2AA
<b>Model:</b>	ELMCL21L
<b>Color:</b>	Gunmetal Gray
<b>Power Source:</b>	Two "AA"
<b>ANSI/NEDA:</b>	15-LF Series
<b>Lamp:</b>	One Cree® XRE LED
<b>Lamp Life:</b>	Lifetime
<b>Lamp Output:</b>	110 Lumens
<b>Typical Weight:</b>	114.8 grams with Energizer e2 lithium batteries
<b>Dimensions (mm):</b>	159.5 x 28.4

### Performance:



### Important Notice

This datasheet contains information specific to products manufactured at the time of its publication  
**Contents herein do not constitute a warranty**  
©Energizer / All Rights Reserved