

Mains cable

Mains cable Copper unshielded , 300/500 V white



FEATURES:

Light duty cable

Class 5 flexible copper conductor

For use in domestic appliances and light portable appliances

Unsuitable for outdoor use or industrial applications

SPECIFICATION:

Cable type	Mains cable
Wire Code	H05VV-F
Conductor	Copper
Sheath colour	white
Shielding	unshielded
Conductor insulation	PVC
Original packaging	50 m
Sheath	PVC
Min. bending radius, moving	8 x line \varnothing
Temperature range	-5...60 °C

PRODUCT RANGE:

Art. no.	Cross-section	Cores	Core colours	\varnothing Sheath
RND 475-00023	0.75 mm ²	2	blue/brown	6.3 mm
RND 475-00025	1.00 mm ²	2	blue/brown	6.6 mm
RND 475-00027	1.50 mm ²	2	blue/brown	7.4 mm
RND 475-00028	2.50 mm ²	2	blue/brown	9.1 mm
RND 475-00030	0.75 mm ²	3	green/yellow/blue/brown	6.7 mm
RND 475-00032	1.00 mm ²	3	green/yellow/blue/brown	7 mm
RND 475-00034	1.50 mm ²	3	green/yellow/blue/brown	8.1 mm
RND 475-00036	2.50 mm ²	3	green/yellow/blue/brown	9.9 mm
RND 475-00038	0.75 mm ²	4	green/yellow/brown/black/grey	7.3 mm
RND 475-00040	1.00 mm ²	4	green/yellow/brown/black/grey	7.9 mm
RND 475-00042	1.50 mm ²	4	green/yellow/brown/black/grey	9 mm
RND 475-00044	2.50 mm ²	4	green/yellow/brown/black/grey	10.8 mm
RND 475-00046	0.75 mm ²	5	green/yellow/brown/black/grey/blue	8.1 mm
RND 475-00048	1.00 mm ²	5	green/yellow/brown/black/grey/blue	8.6 mm

Art. no.	Cross-section	Cores	Core colours	∅ Sheath
RND 475-00050	1.50 mm ²	5	green/yellow/brown/black/grey/blue	10 mm
RND 475-00052	2.50 mm ²	5	green/yellow/brown/black/grey/blue	12.4 mm