



Datenblatt - Fiche technique - Data sheet



21.15.2500



ROLINE Patchkabel Kat.6 UTP, Component Level, LSOH, grau, 0,5 m

Cordon ROLINE UTP Cat.6, LSOH, Component Level, gris, 0,5 m

ROLINE UTP Cable Cat.6 Component Level, LSOH, grey, 0.5 m



1. ELECTRICAL TEST:

- (1). 100% OPEN SHORT & MISS WIRE TEST;
- (2). INSULATION RESISTANCE:DC 250V 20M OHM MIN;
- (3). CONTACTOR RESISTANCE:30 OHM MAX

2. PRINTING:GHMT® roline CAT.6 U/UTP COMPONENT PATCH CORD LSZH 250MHz ISO/IEC 11801 & EN 50173-1 & ANSI/TIA-568-C.2

- 3. 100% Component Patch cord Test PASS
- 4. Minimum bending radius:50mm

MATERIAL LIST

⑥	LABEL	NO DRY GLUE LABEL	1PCS	
⑤	MINI TIE	PE MINI TIE(POSSESS METAL)	2PCS	
④	POLYETHYLENE BAG	POLYETHYLENE BAG	1PCS	
③	OVER MOLD	88A PVC Grey	2PCS	
②	CONNECTOR	RJ45 8P8C' S UNSHIELDED PIN GOLD PLATED 3u",Transparent RED	2PCS	
①	CABLE	U/UTP CAT.6 24AWG (BC*1P)*4+CROSS + JACKET LSOH OD=6.0±0.2MM	1PCS	
NO.	PARTS NAME	SPECIFICATION STANDARD	QT' Y	REMARK

COLOUR:GRAY (RAL 7035)		
ITEM NO.	LENGTH (L)	TOLERANCE (T)
21. 15. 2940	300mm	±10mm
21. 15. 2500	500mm	±15mm
21. 15. 2501	1000mm	±30mm
21. 15. 2504	1500mm	±45mm
21. 15. 2502	2000mm	±60mm
21. 15. 2503	3000mm	±90mm
21. 15. 2505	5000mm	±150mm
21. 15. 2506	7500mm	±210mm
21. 15. 2507	10000mm	±300mm
21. 15. 2508	15000mm	±450mm
21. 15. 2509	20000mm	±600mm

ITEM NO.	21. 15. 2940	21. 15. 2500	21. 15. 2501	21. 15. 2502	21. 15. 2503
21. 15. 2504	21. 15. 2505	21. 15. 2506	21. 15. 2507	21. 15. 2508	21. 15. 2509
DESC.	ROLINE UTP PatchCord CAT. 6, LSOH, Comp. Level, grey				

ARVIN	ALVAN	CHANGE COLOR GREY	2016-11-28	A1
		NEW	2016-10-20	A
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.

