


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **2138150108**
Status: **Active**
Overview: Mega-Fit Power Connectors
Description: Mega-Fit Plug Housing, Single Row, 8 Circuit, UL 94V-0, Glow-Wire Capable, Free Hanging

Documents:

3D Model	Application Specification 768232000-AS-000 (PDF)
Drawing (PDF)	Packaging Specification 2138150001-PK-000 (PDF)
3D Model (PDF)	Datasheet (PDF)
Product Specification 1054171000-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)



General

Product Family	Crimp Housings
Series	213815
Application	Power, Wire-to-Wire
Overview	Mega-Fit Power Connectors
Product Name	Mega-Fit
UPC	193264466412

Physical

Circuits (maximum)	8
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	5.720/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.70mm
Pitch - Termination Interface	5.70mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C, -40° to +120°C

Material Info

Reference - Drawing Numbers

Application Specification	768232000-AS-000
Packaging Specification	2138150001-PK-000
Product Specification	1054171000-PS-000
Sales Drawing	2138150001-SD-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

213815 Series

Mates With

Mega-Fit Receptacle Housing [200456](#)

Use With

Mega-Fit TPA [105415](#)
Mega-Fit Crimp
Terminals [105417](#) , [105418](#)