


Order-No.	Shell Size / for No. of Contacts	B	C	D	E	3	4	$\phi F1$	max I Rubber bushing	H	U	V	5	6	7	8
FMK1G-09S-3360	1 / 9	25	31.6	39.5	15.2	3	-	9.5	6.5	FKT1-2	42	30.8	25	16.4		
FMK2G-15S-3360	2 / 15	33.3	40	41	15.2	3	-	8.5	6.5	FKT1-2	43.5	39.1	33.3	24.7		
FMK3G-25S-3360	3 / 25	47.04	53.7	45	15.2	3	-	8.5	8	FKT1-2A	47.5	53	47.04	38.5		
FMK4G-37S-3360	4 / 37	63.5	70.2	48	18.2	3	-	12	9	FKT3-4	50.5	69.3	63.5	54.9		

FMKYG-XXS-3360

*1) y for hood slot 1, 2, 3 or 4

*2) xx No. of contacts 09, 15, 25 or 37



9	1	Rubber bushing	TPE	black				
8	2	Knurled thumb screw	FRS1/5-K190 4-40 / Brass	nickel plated				
7	0/2	Cable reduction plate	Zinc die-cast	nickel plated				
6	1	Strain relief	ABS	nickel plated				
5	1	Cable clamp	Steel	tin plated				
4	4	Screw	Case hardened steel	zinc plated				
3	2	Catch spring	PEI	black				
2	1	Hood	FMKyG / Zinc die-cast	nickel plated				
1	1	D-Sub Connector	FxxSG2	Surface plating/Colour/Class				

RoHS compliant

max. torque are 40 Ncm
FMK1G-09S-3360 without Part-No. 7
Part-No. 9 not mounted

reverse side
1 : 1

Hood Connector Set

REV.
2
PAGES 1

FKT

a molex company

REPLACEMENT FOR:

FMKyG-xxS-3360

PAGE 1