

Product information

88 01 400

KNIPEX Alligator® XL

Pipe Wrench and Water Pump Pliers

DIN ISO 8976



- The classic model, now also in 400 mm length
- Robust construction, insensitive to dirt; particularly suitable for outdoor work
- Good access to the workpiece due to slim size of head and joint area
- Pinch guard prevents operators' fingers being pinched
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Box-joint design for high stability due to double guide
- Robust adjustment mechanism, insensitive to dirt, easy to clean; particularly suitable for outdoor work
- 11-notch adjustment positioning with a gripping capacity up to 3 1/2", optimised adjustment to the workpiece and user-friendly handle position
- Chrome vanadium electric steel, forged, multi stage oil-hardened

General

Article No.	88 01 400
EAN	4003773075844
Pliers	black atramentized
Head	polished
Handles	with non-slip plastic coating
Weight	1,175 g
Dimensions	400 x 75 x 20 mm
Standard	DIN ISO 8976
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Adjustment positions	11
Capacity for pipes, inches (diameter)	Ø 3 1/2 Inch
Capacities for nuts	95 mm
Capacities for pipes (diameter)	Ø 90 mm

technical change and errors excepted