

**PICCOLO PC C 65 G**



Sample photo

**Order symbol:** PC C 65 G  
**Product nbr:** 8724305  
**Description:** Enclosure, PC  
**Remarks:** Grey cover

**EAN:** 6418074002037  
**El. number:**  
 Finland: 3423405  
 Electric No. 8212001514  
 Denmark:  
 Electric No. Italy: 7201020  
 Electric No. Sweden: 2536807

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	140	80	65	CHM-3	DIN-35 Mounting rail
inch:	5.5	3.1	2.6	FP 22040	Wall fastening lug (2 pcs)

Materials:		Rating:	
<b>Material:</b>	Polycarbonate	Ingress Protection (EN 60529): IP66/IP67	
<b>Base colour:</b>	RAL 7035 -light grey	Impact Resistance (EN 62262): IK08	
<b>Cover screws material:</b>	Polyamide	Electrical insulation: Totally insulated	
<b>Cover colour:</b>	RAL 7035 -light grey	Halogen free (DIN/VDE 0472, Part 815): 1	
<b>Cover screws colour:</b>	Grey	UV resistance: UL 508	
<b>Gasket material:</b>	Polyurethane	Flammability Rating: UL 746C 5"	
		Glow Wire Test (IEC 695-2-1) °C: 960	
		NEMA Class: NEMA 1, 4X, 6, 12, 13	

Temperatures:		Certificates:	
<b>Temperature °C (short term):</b>	-40 ... 120 °C	Germanischer Lloyd (GL)	
<b>Temperature °C (continuous):</b>	-40 ... 80 °C	SGS Fimko	
<b>Temperature °F (short term):</b>	-40 ... 250 °F	Gost R	
<b>Temperature °F (continuous):</b>	-40 ... 175 °F		

Accessories:	
C-MP	Mounting plate

