



4W

VT-834 4W LED WALL LIGHT(ROUND) COLORCODE:4000K IP65-WHITE BODY

Lumens 440	Beam Angle 90	Dimensions Ø112mm
----------------------	-------------------------	-----------------------------

Day White
 SKU:8552



Technical Information

Watts:	4	IP Rating:	IP65
Lumens:	440	Dimmable:	No
Shape:	Round	Warranty (Years):	2
Beam Angle:	90	PF:	>0.45
Unit Color:	White	CRI:	>80
Body Type:	Aluminium	Operation Temperature:	-20 to +45°C
Long life:	20,000 Hours	Input Power:	AC:220-240V,50/60Hz
LED Chip Type:	SMD	Sensor Compatibility:	Yes

Features

- ✓ Perfect choice for Interior and Exterior aesthetics
- ✓ Wall washer to create attractive beam designs
- ✓ High quality LED Chips for reliable lighting effect
- ✓ IP65 rated solid ingress protection
- ✓ Glass screen for controlled light beams
- ✓ Available in different color options - Warm White and Day White
- ✓ Applications - Outdoor, Façade, Residential, Restaurants, Building and many more



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.63
Unit CBM	0.00164

Listing Details

EAN Code	3800157640466
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
---------------------------------	----

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES