


## Myriad Square IP65 White Reflector - White Bezel

MYRIAD SQUARE IP65 FLOOD 2.7K DALI WHTREF WBEZ  
2059017



### Product features

- MYRIAD SQUARE IP65 FLOOD 2700K DALI WHITE REFLECTOR WHITE BEZEL

## PRODUCT OVERVIEW

Product name	MYRIAD SQUARE IP65 FLOOD 2.7K DALI WHTREF WBEZ
Technology	LED
Environment	Interior
General application	Hospitality, Office, Retail, Residential & Consumer
ETIM Class	EC001744
Warranty	5 years
Fixture luminous flux (lm)	720
Luminaire efficacy (lm/W)	48
LOR (%)	100
Colour temperature (K)	2700
Light colour	Candlelight
CRI (Ra)	85
Colour Variation Initial (SDCM)	SDCM3
Beam Angle (°)	48
Photobiological Risk Group	RG1
Total power consumption (W)	15
Electrical protection	Class II
IP rating	IP65/20
IK rating	IK02
Product EAN number	5025768590179

## DATA TABLE

### General data

Product name	MYRIAD SQUARE IP65 FLOOD 2.7K DALI WHTREF WBEZ
Technology	LED
Environment	Interior
General application	Hospitality, Office, Retail, Residential & Consumer
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001744
Warranty	5 years

### Optical data

Fixture luminous flux (lm)	720
Luminaire efficacy (lm/W)	48

## Myriad Square IP65 White Reflector - White Bezel

*MYRIAD SQUARE IP65 FLOOD 2.7K DALI WHTREF WBEZ*  
2059017

LOR (%)	100
Colour temperature (K)	2700
Light colour	Candlelight
CRI (Ra)	85
Colour Variation Initial (SDCM)	SDCM3
Adjustable chromaticity	N
Beam Angle (°)	48
Photobiological Risk Group	RG1

### Electrical data

Total power consumption (W)	15
Mains voltage (V)	230-240V~
Electrical protection	Class II
Transformer required	Yes
Drive current (mA)	350
Energy Efficiency Class (A->G) of contained light source	E
Nominal Frequency (Hz)	50/60Hz

### Lifetime data

Lifespan L70 B50	50000
------------------	-------

### Physical data

IP rating	IP65/20
IK rating	IK02
Reflector finish	White
Nominal Product Width (mm)	72
Nominal Product Height (mm)	64
Cutout Dimensions (W x L in mm or Diameter in mm)	72
Max. Lamp Diameter (mm) - D	90
Weight (kg)	0.37
Recessed Depth (mm)	64

### Packaging

Single packaging type	Carton
Product EAN number	5025768590179
Packaging single length / height (cm)	17.5
Packaging single width (cm)	15.0
Packaging single depth (cm)	17.5
DUN14 (outer)	05025768590179
Units per outer package	1
Packaging outer length / height (cm)	17.5
Packaging outer width (cm)	15.0
Packaging outer depth (cm)	17.5

## PHOTOMETRY