

## Miniature brushes round/cup/wire end brushes

Shank-Ø 2.34 mm and 3 mm

**ATORN**<sup>®</sup>

### Application

For cleaning and polishing as well as for light deburring work in holes and cavities. Due to the low trim width, targeted processing is possible in hard-to-reach spots.

<b>Art. no.</b>	<b>76086 031</b>
<b>Type</b>	Cylinder wire brush
<b>Edging material</b>	Natural bristle goat hair
<b>Max. rotation speed</b>	25000 rpm
<b>Number of pieces per packet</b>	12

### EAN-Code

4050293449310

