



MASTER TL5 Colored

MASTER TL5 HO Colored 54W Red 1SL

Fluorescent lamps with a diameter of 16 mm

Product data

• General Characteristics

System Description	High Output
Cap-Base	G5
Cap-Base Information	Green Plate
Bulb	T5 [16 mm]
Life to 50% fail	24000 hr
Preheat EL,3h	
Life to 10% fail	19000 hr
Preheat EL,3h	

• Electrical Characteristics

Lamp Wattage	54 W
Lamp Wattage EL 25°C	54 W
Lamp Voltage EL 25°C	121 V
Lamp Current EL 25°C	0.450 A
Dimmable	Yes
Lamp Wattage EL 35°C	53.8 W
Lamp Current EL 35°C	0.460 A
Lamp Voltage EL 35°C	118 V

• Environmental Characteristics

Mercury (Hg) Content	3.0 mg
----------------------	--------

• Light Technical Characteristics

Color Code	150
Color Designation (text)	Red

Chromaticity Coordinate X	565 -
Chromaticity Coordinate Y	328 -
Luminous Flux Lamp EL 25°C	3450 Lm
Lumen Maintenance 2000h	95 %



• Product Dimensions

Base Face to Base Face A	1149.0 (max) mm
Insertion Length B	1153.7 (min), 1156.1 (max) mm
Overall Length C	1163.2 (max) mm
Diameter D	17 (max) mm

• Product Data



Order code	927929015024
Full product code	927929015024
Full product name	MASTER TL5 HO Colored 54W Red 1SL
Order product name	MASTER TL5 HO Colored 54W Red 1SL/20
Pieces per pack	1
Packing configuration	20
Packs per outerbox	20
Bar code on pack - EAN1	8711500611901
Bar code on outerbox - EAN3	8727900895179
Logistic code(s) - 12NC	927929015024
ILCOS code	FDH-54/RED/L/P-G5-16/550
Net weight per piece	104.500 gr

Dimensional drawing



Product	A (Max)	B (Min)	B (Max)	C (Max)	D (Max)
TL5 HO 54W/150 Red	1149.0	1153.7	1156.1	1163.2	17

Photometric data



© 2011 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2011, June 7
data subject to change