


## XOP

The maximum permissible temperature is 350°C for the pinch and 650°C for the bulb.



Dimensions in mm

Lamp type	W	Ignition supply V	Lamp current (A)	Luminous Efficacy	Dimmable	Cap-base	Cap-base information	Life to 50% failures	Operating position	Pces per pack	Article no.
XOP 7 -OF 1CT/4	650	207	12.3	20-25 lm/W	No	Ceramic 15.8x14.7mm	Cable 115mm	250 hr	any	4	9283 768 05102
XOP 15-OF 1CT/6	1000	207	10.7	20-25 lm/W	No	Ceramic 15.8x14.7mm	Cable 115 mm	250 hr	any	6	9283 769 05102
XOP 25-OF 1CT/6	1100	207	10.5	20-25 lm/W	No	Ceramic 15.8x14.7 mm	Cable 115mm	250 hr	any	6	9283 775 05102

Product	C (max)	D (max)	O	U	X
XOP 7 -OF	241	12	158 ± 3	14.7 ± 0,35	115 ± 5
XOP 15-OF	395	12	312 ± 3	14.7 ± 0,35	115 ± 5
XOP 25-OF	540	12	457 ± 3	14.7 ± 0,35	115 ± 5

