



- Protection level: IP67  
 - Temperature range: -25°C ... +85°C

Electrical data:  
 -Rated voltage: 15-30V DC  
 -Nominal: 2 A per Contact  
 -Current: 6 A max total

|          |                  |                               |           |
|----------|------------------|-------------------------------|-----------|
| 6        | 090700101150     | PVC, 2xAWG20 + 8xAWG24, black | 10        |
| 5        | 090700101151     |                               | 5         |
| 4        | 090700101153     |                               | 2         |
| 3        | 090700101100     | PUR, 2xAWG20 + 8xAWG24, black | 10        |
| 2        | 090700101101     |                               | 5         |
| 1        | 090700101103     |                               | 2         |
| Cont. no | HARTING part no. | Type of cable                 | Dim. a[m] |

|   |                     |                                      |                                  |  |                    |                        |
|---|---------------------|--------------------------------------|----------------------------------|--|--------------------|------------------------|
|   | All rights reserved | Created by<br>STOCHECIC<br>Stocheici | Inspected by<br>COSTEA<br>Costea | Standardisation<br>MUNTEANV<br>Muntean                   | Date<br>2020-06-16 | State<br>Final Release |
|   | Department HCS - RO | Title<br>har-SAB M8/4/4p PAC         |                                  | Doc-Key / ECM-Nr.<br>100689718/UGD/000/F<br>500000174539 |                    | Rev. F                 |
| HARTING Customised Solutions<br>D-32339 Espelkamp |                     | Type<br>TB                           | Number<br>0907001011XX           |  | Page<br>1/1        |                        |