

FLEXIBLE AC CLAMP METER

DCM4010FLEX



- Current measurement up to 3000 Aac
- LCD display (3000 counts)
- Data hold (HOLD)
- Auto-range
- flexible jaw diameter of 7.5mm
- Low battery indicator
- Backlit display



DCM4010FLEX

FLEXIBLE AC CLAMP METER

General	
Display	3000 cuentas
Auto power off	✓
Backlight	✓
Hold	✓
Batteries	AAA x2(R03, LR03, 24D, 24A)
Dimensions	57mm x 220mm x 35mm
Weight	200 g
Normas en cumplimiento	IEC/EN 61243-3:2014
Standards	CAT IV 600V, CAT III 1000V
Accesorios included	Standard test leads, punch
Specs	
AC current	0,01A - 3000 A
TRMS	✓
Jaw Length	25cm
Jaw section	7,5mm
Safety category	CAT IV 600V, CAT III 1000V
Product Code Information	
SKU	KPSDCM4010FLEXCBINT
EAN code	8435394784700
UPC code	810053676615
Pcs/export carton	20