

GN 75 | Knobs

Steel



MATERIAL

Turned and black-oxide steel.

STANDARD EXECUTIONS

- **GN 75-D:** threaded blind hole.
- **GN 75-E:** threaded pin.

SPECIAL EXECUTIONS ON REQUEST

- Zinc-plated steel executions.
- AISI 316 stainless steel executions.

GN 75.5 | Knobs

Stainless steel



MATERIAL

AISI 304 stainless steel, sandblasted matte finish.

STANDARD EXECUTIONS





- **GN 75.5-D:** threaded blind hole.
- **GN 75.5-E:** threaded pin.

FEATURES AND APPLICATIONS

GN 75.5 handles are made of high quality stainless steel which makes them particularly suitable for applications requiring high standards of hygiene.

SPECIAL EXECUTIONS ON REQUEST

- Zinc-plated steel executions.
- AISI 316 stainless steel executions.
- Glossy finish.



GN 75-D

Code	Description	d1	d2	d4	h	tmin	⚖️
GN.38551	GN 75-16-M5-D	16	M5	10	18	7	12
GN.38555	GN 75-20-M6-D	20	M6	12	24	9	23
GN.38559	GN 75-25-M6-D	25	M6	14	29	9	43
GN.38563	GN 75-32-M8-D	32	M8	18	37	12	82
GN.38567	GN 75-36-M10-D	36	M10	20	42	15	119

GN 75-E

Code	Description	d1	d3	d4	h	l	⚖️
GN.38553	GN 75-16-M6-E	16	M6	10	18	10	15
GN.38557	GN 75-20-M8-E	20	M8	12	24	12	30
GN.38561	GN 75-25-M8-E	25	M8	14	29	14	51
GN.38565	GN 75-32-M10-E	32	M10	18	37	16	98
GN.38569	GN 75-36-M12-E	36	M12	20	42	18	144

GN 75.5-D



Code	Description	d1	d2	d4	h	tmin	⚖️
GN.38581	GN 75.5-16-M5-D-MT	16	M5	10	18	7	12
GN.38585	GN 75.5-20-M6-D-MT	20	M6	12	24	9	23
GN.38589	GN 75.5-25-M6-D-MT	25	M6	14	29	9	43
GN.38593	GN 75.5-32-M8-D-MT	32	M8	18	37	12	82
GN.38597	GN 75.5-36-M10-D-MT	36	M10	20	42	15	119

GN 75.5-E



Code	Description	d1	d3	d4	h	l	⚖️
GN.38583	GN 75.5-16-M6-E-MT	16	M6	10	18	10	15
GN.38587	GN 75.5-20-M8-E-MT	20	M8	12	24	12	30
GN.38591	GN 75.5-25-M8-E-MT	25	M8	14	29	14	51
GN.38595	GN 75.5-32-M10-E-MT	32	M10	18	37	16	98
GN.38599	GN 75.5-36-M12-E-MT	36	M12	20	42	18	144