


SPECIFICATION

- a. Sensitivity : -57dB @ 1kHz (25°C)
- b. Impedance : 20MΩ
- c. Frequency range : 200 to 8000Hz
- d. Capacitance : 15,000pF
- e. Operating temperature : -20°C to +60°C
- f. Storage Temperature : 70°C
- g. Humidity : 85%

DIMENSIONS



- Element : Ceramic element
- Material :
- 1. Acrylic
 - 2. GPS
 - 3. Twist wire (0.8m)
 - 4. Ø3.5mm plug