

MVP12, 6XM12, MOSA, PLUGGABLE CABLE



10.0m PUR-JB 12x0,34+5x0,75

quick connection elements included
with LED for digital PNP-signals 24 V DC
6-way, 5-pole, MOSA
PUR/PVC
10.0 m
potentially separated


Further cable lengths on request. Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)

Illustration



for 2 signals per port



Product may differ from Image

Technical Data

Operating voltage	24 V DC
Signal per port	2
Operating current per contact	max. 4 A
Total current	max. 2 × 8 A
Connection cross section	0.25...0.5 mm ²
Locking of ports	Cap nut
Housing	Plastic, flame retardant
Protection	IP67 inserted and tightened (EN 60529)

Cables

No./diameter of wires	12×0.34 + 5×0.75 mm ²
C-track properties	2 Mio.
Material (jacket)	PUR/PVC
Outer diameter	approx. 11.5 mm
Bend radius (moving)	12 × outer Ø
Cable number	392

General data

Temperature range	-20...+80 °C
-------------------	--------------

Contact layout

Contact 1	(+)
Contact 2	(NC)/(S2)
Contact 3	(-)
Contact 4	(NO)/(S1)
Contact 5	(Earth)
LED display	LED (green): Power / LED (yellow): (S1/S2)

Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1