


MIRO TH 230VAC FK OPTO-COUPLER MODULE



IN: 250 VAC - OUT: 250 VAC / 0,5A

Triac 0.5 A
230 V AC
Spring clamp terminals

[Link to Product](#)

Illustration





Product may differ from Image

Approvals



Input

Voltage range ON	140...250 V AC
Voltage range OFF	0...80 V AC
Control current	7 mA
LED display	LED (yellow)

General data

Test isolation voltage	2.5 kV
Mounting method	DIN-rail mountable (EN 60715)
Housing	Black plastic, flame retardant
Temperature range	-20...+60 °C
Dimensions H × W × D	78×6.2×65 mm

Output

The information in this brochure has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 05/15

Switching voltage	12...250 V AC
Switching current per output	2 mA...0.5 A
Saturation voltage (across output)	max. 1.5 V AC
Leakage current (output is open)	max. 0.3 mA
Switching time ON/OFF	10/10 ms
Switching frequency	max. 20 Hz, depending on suppression

Commercial data

country of origin	CZ
customs tariff number	85414090
minimum order quantity	1