



MAK 30 S grau/grey

Industrial Connectors:Connectors for audio, video and data:Miniature multipole connectors:without locking screw:Straight sockets


Delivery informations

| | |
|---------------------|------------|
| Availability | available |
| Document created at | 18.06.2008 |

Product description

| | |
|--------------------|--|
| Type | MAK 30 S grau/grey |
| Order No. | 930 149-517 |
| Type of contact | female |
| Description | socket with insulated handle; solder joint |
| Housing Color | grey |
| Number of contacts | 3 |
| Conductor size | $\leq 0.34 \text{ mm}^2$ |

Drawing



Technical data

| | |
|----------------------|--------------|
| LF output "Phone" | EN 60 130-09 |
| Pole arrangement DIN | DIN 41 524 |
| Rated current | 4 A |
| Rated voltage | AC/DC 34 V |
| Cable diameter | 5.5 mm |
| Type of termination | solder |

Material

| | |
|--|----------------------------------|
| Contact material (socket) | brass |
| Contact surface material | tin plated |
| Contact bearer material | PA 66/UL standard 94V-2 |
| Housing material | PE |
| Environmental conditions | |
| Protection class (IEC 60529) | IP 30 |
| Temperature range | -20 °C to +60 °C |
| Scope of delivery and accessories | |
| Packaging | retail package, polyethylene bag |