
# DATA SHEET PULLING ROPE POLYESTER Ø 10 mm incl. reel







D	٨	т	۸
	~		

DATA			
ITEM NO.	10167	10168	
LENGTH ROPE	120 m	200 m	
Ø ROPE	10 mm		
REEL BASKET Ø ca.	514 mm	730 mm	
INTERNAL BASKET ca.	70 mm	98 mm	
DIMENSION	L 550 x B 220 x H 650 mm	L 820 x B 400 x H 900 mm	
TOTAL WEIGTH KG	16 kg	28 kg	
TOTAL BREAKING LOAD	1640 kg		
MATERIAL ROPE	Polyester-Rope		
LOOP	2 x spliced-in loops		
EAN CODE	9120045475906	9120045475913	

### DESCRIPTION

RUNPOTEC polyester pulling ropes are optimally suited for horizontal cable pulling with the RUNPOTEC CW 800 E capstan winch. RUNPOTEC recommends using the connecting swivel with twist compensation for horizontal cable pulling. It reduces frictional resistance and protects the cable and the feed system.

The reel allows controlled winding and unwinding of the rope. In addition, the rope is perfectly stowed away and ready for use at any time. The 770 mm reel cage size can be easily rolled and transported due to the integrated wheels.



#### Safety instructions:

Not suitable for vertical cable pulling, must not be used to carry or lift loads or persons.

**Optimal application:** for horizontal cable pulling in combination with the CW 800 E capstan winch

Application video: a short, very informative application video can be viewed by scanning the QR code or on www.runpotec.com. Scope of delivery: pulling rope polyester Ø 10 mm incl. reel

## ADVANTAGES

- Spliced loops at the start and end of the rope
- ✓ Low rope elongation
- Practical reel for controlled winding and unwinding of the rope
- Reel Ø 530 mm with extendable feet
- ✓ Reel Ø 730 mm mobile with wheel
- Reel with parking brake

#### INFORMATION

